

International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com



GENERAL PURPOSE ROUND SPEAKERS

Part Number: S400RA

MODEL NUMBER	S400RA
FRAME DIAMETER (MM)	102
FRAME DEPTH (MM)	33
MATERIAL: CONE / FRAME	PAPER / METAL
MAGNET TYPE	ALNICO
MAGNET: SIZE (MM) / WEIGHT (OZ/GRAMS)	13 x 10 - 0.35 / 9.92
RATED POWER (WATTS): Nom. / Max.	0.5 / 1.0
VOICE COIL IMPEDANCE (OHMS)	8 ± 15% @ 800 Hz 1V
RESONANT FREQUENCY (Hz) Without Baffle	
FREQUENCY RESPONSE (Hz)	Fo ~ 20000
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	91 ± 3 dB
MEASURED AT:	1W @ 50 CM
MEAN VALUE AT:	300, 400, 500, 600 Hz
OPERATION (MUST BE NORMAL)	<u> </u>
BUZZ & RATTLES (MUST BE NORMAL)	PROGRAM SOURCE 1 W
DISTORTION @ RATED POWER INPUT	SINE WAVE 0.5 W
LOAD TEST (WHITE NOISE)	5% MAXIMUM @ 1,000 Hz
HUMIDITY TEST*	0.5W @ 5 HOURS
	40° ± 2°C 90% R.H. 96 HRS

HEAT TEST*	40° ± 2°C 50% R.H. 96 HRS
OUTSIDE DIAMETER OF YOKE SEAT (MM)	22 - YOKE SIZE: 22 x 14.2 x 12.5
OUTSIDE DIAMETER (ELIMINATE RIM)	93
BAFFLE OPENING (MM)	93
THICKNESS OF RIM (MM)	3.7
NET WEIGHT (OUNCES/GRAMS)	2.40 / 68

POLARITY:

DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.

*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS

DIMENSIONS

■ TYPICAL FREQUENCY RESPONSE CURVE

Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved.

This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)