


VOLEX GROUP

Standard Cord Details: 17600 10 B1



	Specifications
Certifications	<b>(4)</b> (4)
Part Number	17600 10 B1
Connector Type	C13
Plug Type	5-15P
Category	Plastic
Application	Detachable
Plug Catalog No.	PS204
Connector Catalog No.	386A
Cable	SJT AWG 18x3 (Shielded)
Jacket Color	black
Length in Feet	6'7
Length in Meters	2
Temperature Rating	60 C
Packaging Units Per Carton	H-100,H-25,S-25
Color Coding	International
Nominal OD in Inches	0.328
Nominal OD in Millimeters	8.33
Notes	See 17729 for 105C version. See 17742 for SVT version. See 17500 for unshielded version.





PACKAGING: FOLD & TIE

- Volex FORM IN71-07 REV.A
- Indianapolis, IN
- □ Conover, N.C. ☐ Freemont, CA
- ☐ Aguascalientes, MX
- ☐ Tijuana, Mexico
- ☐ Hermosillo, MX ☐ Clinton, AR
- ☐ Kanata, Canada

## Proprietary Notice:

This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone without the express written consent of Volex Inc.

## MATERIAL:

PLUG: PVC, BLACK JACKETI PVC, BLACK

FINISH

JACKET: SMOOTH

## NOTES:

- 1) CORDAGE: 18/3/SJTS/60\*C/BLACK
- 2) APPROVALS: (IDS)

E0. ± X.

FRACT. ± 1/32 ANGULAR ± 1/2\*

- 3) RATING: 10 AMP/125 VOLTS
- 4) FLAME RATING : FT2
- 5) CORDAGE D.D. : .328 (REF.)
- 6> PACKAGING: 100 PIECES/CARTON
- 7) ALL DIMENSIONS IN inches.

2		08/20/04						
1		06/11/04						
REV	DESCRIPTION DATE							
SCALE NOT SCA	TD CORDSET - NORTH AMERIC							
TOLERANCE UNLESS OTHERVISE SPECIFIED		THERWISE	APPROVED CR	DRAWN BY ARK	DATE	6/11/04		

SPECIFIED CR ARK 200. ± XXX. S0. ± XX.

PART NO.

17600 10 B1