


VOLEX GROUP

Standard Cord Details: 17250 10 B1




Specifications		
Certifications	(1) (1) (1)	
Part Number	17250 10 B1	
Connector Type	C13	
Plug Type	5-15P	
Category	Plastic	
Application	Detachable	
Plug Catalog No.	US15S3	
Connector Catalog No.	386A	
Cable	SVT AWG 18x3	
Jacket Color	Black	
Length in Feet	7.5	
Length in Meters	2.29	
Temperature Rating	60C	
Packaging Units Per Carton	100	
Color Coding	North America	
Nominal OD in Inches	0.246	
Nominal OD in Millimeters	6.25	
Notes	SEE ALSO THE 17249 FOR A 6FT VERSION. Same as 17251 except for color code.	





PACKAGING: FOLD & TIE



V
Volex
CUD
FORM IN71-07 REV.A

☐ Conover,N.C.
☐ Freemont, CA
☐ Aguascalientes, MX
☐ Tijuana, Mexico
☐ Hermosillo, MX
☐ Clinton, AR
□ Kanata, Canada

☑ Indianapolis, IN

without the express written consent of Volex Inc.

NOTES:

- 1) CORDAGE: 18/3 SVT, 60°C, BLACK
- 2) APPROVALS: (II)
- 3) RATING: 10 AMP/125 VOLTS
- 4) FLAME RATING : FT2
- 5) PACKAGING: 100 PIECES/CARTON
- 6) ALL DIMENSIONS IN MILLIMETERS.

SCALE	E: ECD:	ITEM DESCRIPTION	
RE∨	DESCRIPTION		DATE
2	FORMAT UPDATE		8/16/04
3	CHA	8/30/04	
4	REVISED T□	SHOW CHINA MANUFACTURED CORD	11/26/07

Proprietary Notice:
This document is the property of Volex Incorporated. The information contained herein is not to be disclosed to anyone

MATERIAL:

FINISH:

PLUG: PVC, BLACK JACKET: PVC, BLACK

RoHs/Prop 65 Compliant

UNLESS OTHERWISE SPECIFIED .XXX ± .005 JACKET: SMOOTH 20. ± XX. .X ± .03 FRACT. ± 1/32 ANGULAR ± 1/2*

NOT TO N/A SCALE APPROVED TOLERANCE

CORDSET-NORTH AMERICAN DETACHABLE POWER SUPPLY CORD (7.5') DRAWN BY DATE:

STC ARK 06/08/04 PART NO.

17250 10 B1