

Product Datasheet	Catalog Home Home Page Search				
HBL7485 Twist-Lock Plug					
41 [*] (10.4)					
	Product Specifications				
Product Type	Twist-Lock Devices				
Product Item	Plug				
Wiring Scheme	3 Pole, 3 Wire Non-Grounding				
Amperage	15A				
Voltage	125/250V AC				
NEMA Configuration	ML-3P				
Item Style	Standard				
Device Color	Black				
Cord Dia.	.281"421" (7.1-10.7)				
Blade Holder Material	Black Phenolic				
Housing Material	Black nylon				
Cord Clamp Material	Zinc Plated Black Steel				
Blade Material	Brass				
Terminal Screw Material	Brass				

Ground Screw Material	Brass			
Cord Clamp Screw Material	Steel zinc plated			
Body Holding Screw Material	Steel zinc plated			
Ratings	Molded into face			
Dielectric Voltage Withstand	2,000 minimum			
Current Interrupting	Certified for current interrupting at full rated current.			
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .			
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.7 No. 49.			
Terminal Accommodation	15A-#14AWG			
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, White)			
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6			
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)			
Moisture Resistance	IP20			
Listings	UL			
Catalog Page	Click here for catalog page B34			
Brochures	Click here for product brochure			
Hubbellnet	Click here for Hubbellnet			
Catalog Section	Click here for Section-B			
UPC Number	78358523741			
Weight in LBs	0.1			



TWIST-LOCK® Devices 3 Pole, 3 Wire, Non-Grounding 15 Ampere, 125/250 Volts Midget TWIST-LOCK Flanged Receptacles and Plugs

(Ų_)





HBL7485V










HBL7495V

HUBBELL	

B-34



Flanged Receptacles

Description **Catalog Numbers** HBL7487N Exposed terminals, black nylon flange. HBL7487 Exposed terminals, stainless steel flange, _ Covered terminals, stainless steel flange, HBL7489 _ accepts cord .500" (12.7) in diameter.

Male Plugs IP20 SUITABILITY

Description	Cord Dia.	Catalog Number	S
Valise [®] plug, black nylon, with insulation displacement terminals, multiple drive screws.	.300"430" (7.6-10.9)	-	HBL7485V
Black nylon body, phenolic base, multiple drive screw terminals, cord grip.	.281"421" (7.1-10.7)	-	HBL7485
Same as above, except angle cord grip.	.335"421" (8.5-10.7)	-	HBL7432

Weatherproof Boot IP55** SUITABILITY

Description	Catalog Number
Seal-Tite [®] cover, black elastomer, for use with a HBL7485V or HBL7485 plug when used with a HBL7484V or HBL7484	HBL7495V
connector body when used with a flanged inlet.	

Notes: These devices are not interchangeable with any other devices in this catalog. All male ground pins are solid and all female ground contacts have hollow sleeves. **When installed and used properly with plug and connector body combinations. * Not UL Listed.

