

# HBL5662 -- Heavy Duty Specification Grade Duplex Receptacle



Color	
Other Available Colors	Brown Brown, Ivory
NEMA No.	6-15R
Horsepower	1.5
Description	Heavy Duty Straight Blade Duplex Receptacle
Туре	2 Pole, 3 Wire, Grounding
Rating	15A, 250V
Certification	UL Listed to UL 498 File E2186, Guide RTRT Fed Spec WC596G, Meets WD-6 requirements, Certified to CSA, C22.2, No. 42 File 285.
Terminal Screw Material	#8-32 Brass /Ni plated for neutral
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)
Wire Clamps Material	.062" (1.6) Steel - Ni. Plated
Top Material	Nylon
Base Material	Reinforced PET
Power Contacts Material	.037" (.9) Phosphor Bronze
Mounting Strap Material	.050" (1.3) Brass
Center Assembly Rivet Material	Brass
Auto Ground Clip Material	Stainless Steel
Mounting Screw Material	Stainless Steel
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	Top: UL 94 V2. Base: UL 94 V0 and UL 94-5 VA.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
M Drawings	Click here for M-Drawing

Catalog Page	Click here for catalog page A25
Brochures	Click here for product brochure
Catalog Section	Click here for Section-A
UPC Number	78358543554
Weight in LBs	0.25





### Straight Blade Devices **2 Pole, 3 Wire Grounding** 15 and 20 Ampere, 250 Volts

Heavy Duty, Specification Grade Receptacles







- 6

20A 250 UL CSA

NEMA

Heavy Duty, Specification Grade, Duplex Receptacles

Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired,	Brown Ivory	HBL5662 HBL5662I	HBL5462 HBL5462I
multiple drive screws.	Gray	-	HBL5462GY
Isolated ground.	Orange	IG5662	IG5462

#### Heavy Duty, Hospital Grade, Duplex Receptacles

Description Color Catalog Number		bers	
Flush, thermoplastic polyester face, back and side wired, multiple drive screws.	Brown	HBL8600	HBL8400
	Ivory	HBL8600I	HBL8400I

## Heavy Duty, Specification Grade, Single Receptacles

Description	Color	Catalog Numbers	
Flush, nylon face, back & side wired.	Brown Ivory	HBL5661 HBL5661I	HBL5461 HBL5461I
Isolated ground.	Orange	IG5661	IG5461
Panel mount 1.94" (49.3) centers.	Brown	HBL5684	-


## Compact, Specification Grade, Duplex and Panel Mount Single Receptacles

Description	Color	Catalog Numbers	
Flush, nylon face, side wired only.	Brown	HBL5652 –	
	lvory	HBL5652I –	
Panel mount 1.75" (44.5) centers.	Brown	HBL5658 –	


Notes: HP ratings are AC only.


See page A-38 for accessories.

See Section J for full line of isolated ground devices.


















HUBBELL