


## WP2 -- Weatherproof Covers



For all 4 & 5 Wire 20A & 30A Insulgrip Flanged Units

WP2

Product Specifications	
<b>Product Type</b>	 <p><b>Accessories</b></p>
<b>Accessory Type</b>	Weatherproof Covers
<b>Plate Type</b>	1-Gang
<b>Plate Material</b>	Thermo-Plastic
<b>For Use With</b>	20 & 30A Flanged Device
<b>Plate Mounting</b>	FS/FD Mount
<b>Device Color</b>	Gray
<b>Catalog No</b>	Permanently ink marked on product
<b>Flammability</b>	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.
<b>Operating Temperatures</b>	Maximum Continuous 75 C Minimum -40 C (w/o impact)
<b>Moisture Resistance</b>	IP44
<b>Listings</b>	UL/CSA
<b>Catalog Page</b>	<a href="#">Click here for catalog page B50</a>
<b>Catalog Section</b>	<a href="#">Click here for Section-B</a>
<b>UPC Number</b>	783585392288
<b>Weight in LBs</b>	0.3

