

Product Datasheet


Catalog Home Home Page Search

P050NBKA -- Liquidtight System



P075NGYA

Product Specifications

Product Type	Liquidtight System
Liquidtight System Type	Flexible Nonmetallic Liquidtight Connectors
Liquidtight Connector Body Style	Straight
Trade Size	1/2"
Color	 Black
Effective Operating Temperature	-30°F to +225°F (-34°C to +107°C).
Recommended Knockout Hole Size	.86 - .91" (21.8 - 23.0)(mm)
Flammability	Nylon PolyTuff connectors have a UL 94-V2 rating, New York State Office of Fire Prevention and Control-Construction Specification Institute number 16111.
Dimension A	1.30" (33.0)
Dimension B	2.14" (54.4)
Dimension C	.57" (14.5)
Dimension D	.55" (14.0) Throat Dia.
Dimension E A/C	1.41" (35.8)
Dimension E A/F	1.30" (33.0)
Certifications	UL Listed, CSA Certified
UPC Number	78358533912
Weight in LBs	0.05
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

