

Product Datasheet

[Catalog Home](#)
[Home Page](#)
[Search](#)

SHC1012 -- Cord Connectors



Machined
Aluminum

Hubbell offers a full line of machined aluminum cord connectors in N.P.T. hub sizes 1/4" through 1" and cast aluminum 1" to 3". They provide durable performance and a clean attractive look without adding unwanted weight.

Product Specifications

Product Type	Cord Connectors
Material/Style	Aluminum
Cord Diameter Range	.38"-.44" (9.5-11.0)
Cord Connector Body Style	Straight Male
Form Size	F1
HUB Size	3/8"
Color Code	Blue
Effective Operating Temperature	-30°F to +225°F (34°C to +107°C)
Recommended Knockout Hole Size	.67"-.70" (17.0-17.8)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	.88" (22.4) Dia.
Dimension B	.90" (22.9) Ref.
Dimension C	.46" (11.7)
Dimension D	.44" (11.2) Throat Dia.
Dimension E A/C	.99" (25.1)
Dimension E A/F	.88" (22.4)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UPC Number	78358520012
Weight in LBs	0.1
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



