

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

SHC1044 -- Cord Connectors

Machined
Aluminum

Hubbell offers a full line of machined aluminum cord connectors in N.P.T. hub sizes ¼" through 1" and cast aluminum 1" to 3". They provide durable performance and a clean attractive look without adding unwanted weight.

Product Specifications

Product Type	Cord Connectors
Material/Style	Aluminum
Cord Diameter Range	1.00" - 1.13" (25.4- 28.6)
Cord Connector Body Style	Straight Male
Form Size	F4
HUB Size	1"
Color Code	Pink
Effective Operating Temperature	-30°F to +225°F (34°C to +107°C)
Recommended Knockout Hole Size	1.36" - 1.41" (34.5-35.7)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	1.75" (44.4) Dia.
Dimension B	1.60" (40.6)
Dimension C	.71" (18.0)
Dimension D	1.02" (25.9) Throat Dia.
Dimension E A/C	1.81" (46.0)
Dimension E A/F	1.62" (41.1)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UPC Number	78358520044
Weight in LBS	0.3
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



