
Product Datasheet Catalog Home Home Page Search

# HBL2333 -- Twist-Lock Connector Body



1.97" 2P3W, 20A 277V AC, L7-20R, Black & White Nylon

HBL2313

# **Product Specifications**

Product Type	Twist-Lock Devices
Product Item	Connector Body
Wiring Scheme	2 Pole, 3 Wire Grounding
Amperage	20A
Voltage	277V AC
NEMA Configuration	L7-20R
Item Style	Insulgrip
Device Color	Black/White
Cord Dia.	.360"930" (9-24)
Terminal Retainer Material	Clear polycarbonate
Housing Material	Black nylon
Cord Clamp Material	Natural (white) nylon
Terminal Clamp Material	.08" (2) steel-nickel plated
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive

<b>Ground Screw Material</b>	#10-32 Brass (green finish) Multi-drive
Cord Clamp Screw Material	Steel, zinc plated Multi-drive
<b>Body Holding Screw Material</b>	Steel, zinc plated Multi-drive
<b>Body Contact Carrier Material</b>	Natural White Nylon
<b>Contact Spring Material</b>	Brass
Spring Binding Plate Material	Brass
<b>Ground Contact Material</b>	.031" (.8) Brass
Ratings	Molded into face.
Catalog No.	Permanently ink marked on body.
Dielectric Voltage Withstand	2,000V minimum
<b>Current Interrupting</b>	Certified for current interrupting at full rated current.
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	20A #12 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
<b>Operating Temperatures</b>	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Listings	FED SPEC UL/CSA
Feature Info	Black and white nylon.
Catalog Page	Click here for catalog page B22
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
<b>Catalog Section</b>	Click here for Section-B
UPC Number	78358503792
Weight in LBs	0.35
,	



NEMA Configuration



### TWIST-LOCK® Devices

# 2 Pole, 3 Wire Grounding

20 Ampere, 125, 250 Volts and 277 Volts AC

## Receptacles, INSULGRIP® Connector Bodies, Flanged Devices and Plugs






HBL2313





HBL2311







# Single Flush Receptacles, Back and Side Wired Description Ca

NEMA L5-20R	NEMA L6-20R			
20A 125V	20A 250V			
UL/CSA	ULICSA			
1 HP	2 HP			
Catalog Numbers				



Dack and Side Wifed	1 HP	2 HP	2 HP
Description	Catalog Numbers		
Black nylon face.	HBL2310	HBL2320	HBL2330
Isolated ground, orange nylon face.	IG2310	IG2320	_
Corrosion resistant, yellow nylon face.	HBL23CM10	_	_

# Insulgrip Connector Bodies IP20 SUITABILITY

Description	Catalog Numbers		
Black and white nylon.	HBL2313	HBL2323	HBL2333
Corrosion resistant, yellow nylon.	HBL23CM13	HBL23CM23	-

Note: Cord clamp range .360"-.930" (9-24).

### **Insulgrip Flanged Receptacles**

Description	Catalog Numb	ers	
Nylon casing, back wired.	HBL2316	HBL2326	HBL2336







### Insulgrip Plugs IP20 SUITABILITY

Description	Catalog Numb	ers	
Black and white nylon.	HBL2311	HBL2321	HBL2331
Corrosion resistant, yellow nylon.	HBL23CM11	HBL23CM21	_

Notes: Cord grip range .360"-.930" (9-24). See page B-73 for Add-A-Shroud™ kit.

#### **Insulgrip Flanged Inlets**

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2315	HBL2325	HBL2335

Notes: See pages B-68 and B-69 for accessories. See page B-63 for switched enclosure. For technical information see page B-83. HP ratings are AC only. Only receptacles and plugs are HP rated.

HUBBELL Wiring Device-Kellems