HBL2431 -- Twist-Lock Plug



2.33 3P4W, 20A 3PH 480V AC, L16-20P, Black & White Nylon

HBL2411

Product Specifications

Product Type Twist-Lock Devices **Product Item** Plug Wiring Scheme 3 Pole, 4 Wire Grounding Amperage 20A 3 Phase 480V AC Voltage **NEMA Configuration** L16-20P **Item Style** Insulgrip **Device Color** Black/White Horsepower Cord Dia. .35"-1.15" (9-29) Natural White Nylon **Blade Holder Material Terminal Retainer Material** Clear polycarbonate **Housing Material** Black nylon **Cord Clamp Material** Natural (white) nylon

D
Brass
.08" (2) steel-nickel plated
#10-32 Brass (white finish on neutral screw when used) Multi-drive
#10-32 Brass (green finish) Multi-drive
Steel, zinc plated Multi-drive
Steel, zinc plated Multi-drive
Molded into face
Permanently ink marked on body.
2,000V minimum.
Certified for current interrupting at full rated current.
Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
20A #12 AWG
Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
HB or better per UL 94 or CSA 22.2 No. 0.6
Maximum Continuous 75 C Minimum -40 C (w/o impact)
IP20
FED SPEC UL/CSA
Black and white nylon.
Click here for catalog page B37
Click here for product brochure
Click here for Hubbellnet
Click here for Section-B
78358503827
0.25



NEMA Configuration



TWIST-LOCK® Devices

3 Pole, 4 Wire Grounding

20 Ampere, 125/250 Volts, 3Ø 250 and 3Ø 480 Volts AC


Receptacles, INSULGRIP® Connector Bodies, Flanged Devices and Plugs





Single Flush Receptacles,

Back and Side Wired	UL/CSA 2 (1) HP	UL/CSA 3 HP	UL/CSA 5 HP
Description	Catalog Numbers		
Black nylon face.	HBL2410	HBL2420	HBL2430
Isolated ground, orange nylon face.	IG2410	IG2420	_



Insulgrip Connector Bodies IP20 SUITABILITY

Description	Catalog Numbers		
Black and white nylon.	HBL2413	HBL2423	HBL2433
Corrosion resistant, yellow nylon.	HBL24CM13	HBL24CM23	HBL24CM33


Note: Cord clamp range .35"-1.15" (9-29).



Insulgrip Flanged Receptacles

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2416	HBL2426	HBL2436





Insulgrip Plugs IP20 SUITABILITY

Description	Catalog Numbers		
Black and white nylon.	HBL2411	HBL2421	HBL2431
Corrosion resistant, yellow nylon.	HBL24CM11	HBL24CM21	HBL24CM31

Notes: Cord clamp range .35"-1.15" (9-29). See page B-73 for Add-A-Shroud™ kit.





HBL2411

Insulgrip Flanged Inlets

Description	Catalog Numbers		
Nylon casing, back wired.	HBL2415	HBL2425	HBL2435

Notes: All HP ratings are AC only.

HP ratings not in parentheses are phase to phase. HP rating in parentheses is phase to neutral. Only receptacles and plugs are HP rated. See pages B-70 and B-71 for accessories. For technical information see page B-83. See page B-63 for switched enclosure.



3P 4W, 20A, 125/250V, 3Ø 250 and 3Ø 480V AC