
HBL5266C -- Insulgrip Series

HBL5266C Insulgrip Series				
	P3W, 15A 125V, 5-15P, Black and White Nylon			
	Product Specifications			
Product Type	Plugs			
Body Style	Straight			
Standard	NEMA			
Amperage	15A			
Voltage	125V			
Poles and Wires	2 Pole, 3 Wire Grounding			
Hospital Grade ?	No			
Plug/Connector Grade	Insulgrip			
Color	Black			
NEMA No.	5-15P			
Horsepower	0.5			
Cord Dia.	.230"720" (5.8-18.3)			
Description	Straight Blade Plug			

Туре	2 Pole, 3 Wire, Grounding	
Rating	15A,125V	
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280	
IP Suitability	IP20	
Housing Material	Nylon-Black	
Blade Holder Material	Nylon-Natural	
Retainer Material	Polycarbonate-Clear	
Cord Clamp Material	Nylon-Natural	
Contact Blades Material	.060" (1.5) Brass	
Ground Contact Blade Material	.040" (1.0) Copper Alloy	
Terminal Screw Material	#8-32 Brass /Ni plated for neutral	
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)	
Wire Clamps Material	.062" (1.8) Steel-nickel finish	
Dielectric Voltage	Withstands 2,000V minimum.	
Current Interrupting	Certified for current interrupting at full rated current.	
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%	
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).	
Terminal Accommodation	#18-#10 AWG copper stranded conductor	
Product Identification	Ratings are a permanent part of the device.	
Flammability	UL 94 HB or better.	
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).	
Certified	UL2305 OEM and replacement use on convention center flat cable cord sets.	
M Drawings	Click here for M-Drawing	
Catalog Page	Click here for catalog page A15	
Brochures	Click here for product brochure	
Catalog Section	Click here for Section-A	
UPC Number	78358517300	
Weight in LBs	0.15	





Straight Blade Devices 2 Pole, 3 Wire Grounding 15 and 20 Ampere, 125 Volts

INSULGRIP® Heavy Duty Plugs

	IP20 SUITABILITY	W B B	U G G G G G G G G G G G G G G G G G G G
Insulgrip Plugs		NEMA 5-15P 15A 125V UL CSA 0.5 HP	NEMA 5-20P 20A 125V UL CSA 1 HP
Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.230"720" (5.8-18.3)	HBL5266C™	HBL5366C™
Corrosion resistant yellow nylon.	.230"720" (5.8-18.3)	HBL52CM66C	HBL53CM66C
8-position angle plug, black and white nylon.	.325"655" (8.3-16.6)	HBL5266CA	HBL5366CA
8-position angle plug, transparent enclosure.	.325"655" (8.3-16.6)	HBL5266CAT	-
Anchor lock, black and white nylon. ⁽¹⁾	.230"720" (5.8-18.3)	HBL5280C	-
Anchor lock, corrosion resistant yellow nylon. ⁽¹⁾	.230"720" (5.8-18.3)	HBL52CM80C	-
Finger grip, black neoprene, combination screws. CSA only.	.312"468" (7.9-11.9)	HBL5921	-
Fusible, black vinyl housing, slotted screws. CSA only.	.296"625" (7.5-15.9)	HBL5299	-

Insulgrip Hospital Grade Plugs

	-		
Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.230"720" (5.8-18.3)	HBL8215C™	HBL8315C
Transparent housing.	.230"720" (5.8-18.3)	HBL8215CT	HBL8315CT
8-position angle plug, transparent housing.	.250"655" (6.4-16.6)	HBL8215CAT	HBL8315CAT

Accessories

Seal-Tite [®] triple seal, black elastomer cover for Insulgrip [®] plugs when used in a cord set, and connector bodies when used with flanged inlets.	HBL6017*
Same as above except yellow.	HBL60CM17*
PLUGOUT [®] Lockout device for Hubbell plugs and others.	HLD

Notes: See page A-39 for accessories. See page A-42 for technical information. ⁽¹⁾UL component listed only. Not for general use applications. *IP55 when installed and used properly with mating components.







HBL5266CA





HBL8215C



