HBL5369C -- Insulgrip Series Connector Body



1.40° 2P3W, 20A 125V, 5-20R, Black and White Nylon (35.6)

Product Specifications

Product Type



Connectors

Body Style	Straight
Standard	NEMA
Amperage	20A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Wiring Method	Back Wire
Hospital Grade?	No
Plug/Connector Grade	Insulgrip

Color




Black

NEMA No. 5

Cord Dia. .230"-.720" (5.8-18.3)

Description	Straight Blade Connector		
Type	2 Pole, 3 Wire, Grounding		
Rating	20A, 125V		
Certification	UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280		
IP Suitability	IP20		
Housing Material	Nylon-Black		
Retainer Material	Polycarbonate-Clear		
Cord Clamp Material	Nylon-Natural		
Terminal Screw Material	#8-32 Brass, Multiple Drive		
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)		
Wire Clamps Material	0.062" (1.6) Steel - Ni Plated		
Body Holding Screws	Steel Multiple Drive		
Contact Holder Material	Nylon-Natural		
Power Contacts Material	.040" (1.0) Copper Alloy		
Dielectric Voltage	Withstands 2,000V minimum.		
Current Interrupting	Certified for current interrupting at full rated current.		
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%		
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).		
Terminal Accommodation	#18-#10 AWG copper stranded conductor		
Product Identification	Ratings are a permanent part of the device.		
Flammability	UL 94 HB or better.		
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).		
M Drawings	Click here for M-Drawing		
Catalog Page	Click here for catalog page A16		
Brochures	Click here for product brochure		
Catalog Section	Click here for Section-A		
UPC Number	78358517425		
Weight in LBs	0.15		





Straight Blade Devices 2 Pole, 3 Wire Grounding 15 and 20 Ampere, 125 Volts

INSULGRIP® Connector Bodies



HBL5269C



HBL8219C













Insulgrip Connector Bodies

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.230"720" (5.8-18.3)	HBL5269C™	HBL5369C™
Corrosion resistant yellow nylon.	.230"720" (5.8-18.3)	HBL52CM69C	HBL53CM69C

Insulgrip Hospital Grade Connector Bodies

Description	Cord Dia. .230"720" (5.8-18.3)	Catalog Numbers	
Black and white nylon.		HBL8219C™ HBL8319C	
Transparent housing.	.230"720" (5.8-18.3)	HBL8219CT	HBL8319CT

Accessories

Seat-Tite® triple seal black elastomer cover for Insulgrip® connector bodies when used in a cord set.	HBL6018*
Same as above except yellow.	HBL60CM18*
Closure plug, black.	HBL6019
Closure plug, yellow.	HBL60CM19
PLUGOUT® lockout device for Hubbell plugs and others.	HLD

Notes: *IP55 suitability if closure plug inserted or when installed and used properly with HBL6017 or HBL60CM17.

www.hubbell-wiring.com