

High Resolution Milliohm Meter

 **Benchtop meter provides resolution down to 0.01m**
Using 4-wire Kelvin clip test leads

Features:

- 7 ranges for wide low resistance measurements
- High resolution to 0.01mΩ
- 1999 count display with 0.8" digits
- Automatic zero
- Built-in comparator for Hi/Lo/Go resistance testing or selection
- 5V test voltage
- One year warranty
- Complete with 4-wire cables with Kelvin clip connectors and power cord



Specifications	Range	Resolution	Current	Accuracy (%rdg)
Resistance	20mΩ	0.01mΩ	1A	±(0.2% + 6d)
	200mΩ	0.1mΩ	1A	±(0.2% + 4d)
	2Ω	0.001Ω	100mA	±(0.2% + 4d)
	20Ω	0.01Ω	10mA	±(0.2% + 4d)
	200Ω	0.1Ω	1mA	±(0.2% + 4d)
	2kΩ	0.001kΩ	100μA	±(0.2% + 4d)
	20kΩ	0.1kΩ	10μA	±(0.2% + 4d)
Power	110VAC, 60Hz or 220VAC 50Hz			
Dimensions/Weight	11 x 8.3 x 3.5" (280 x 210 x 90mm)/ 4.85lb (2.2kg)			

Ordering Information:

380560.....Precision Milliohm Meter, 110VAC
380560-NIST380560 with NIST Certificate
380562.....Precision Milliohm Meter, 220VAC
380562-NIST380562 with NIST Certificate
380465.....Spare Kelvin Clip Test Lead Set

