

Type J/K, Dual Input Thermometer with Alarms

Dual J or K input with dual display
With relative and programmable High/Low audible alarms

Features:

- Widest range with highest 0.05% accuracy
- Rugged design for field use
- Large dual LCD displays T1, T2 or T1-T2, plus Elapsed Time
- Differential temperature between Type J, Type K, or both Type J and K
- MIN/MAX/AVG readings
- Data Hold and Relative functions
- Programmable Hi/Lo audible alarms
- Complete with two Type K bead wire temperature probes (-4 to 482°F/-20 to 250°C), protective holster with stand, and 9V battery



Specifications	
Range, Type K °F (°C)	-328 to 2498°F (-200 to 1370°C)
Range, Type J °F (°C)	-328 to 1922°F (-200 to 1050°C)
Basic Accuracy	±0.05% rdg
Resolution	0.2°F/0.1°C
Dimensions	7.6 x 3.6 x 2.1" (192 x 91 x 53mm)
Weight	13oz (365g)

Ordering Information:

421502Type J/K, Dual Input Thermometer with Alarms
421502-NISTType J/K, Dual Input Thermometer/ Alarms with NIST

