

LED PANEL MOUNT INDICATOR

SUNLIGHT VISIBILITY, PROMINENT BEZEL, AC/DC OPERATION


MOUNTING HOLE, Ø 8mm

PART NO.	COLOR	VOLTAGE	CURRENT	LUMI. INTENSITY	DOMINANT
		V _{OP} [V] AC/DC	I _{OP typ.} [mA] AC/DC	LED **I _{V typ.} [mcd]	WAVELENGTH λ _D [nm]
SATIN CHROME BEZEL					
WL-19080250	RED	12V	9/17	1250	630
WL-19080252	YELLOW	12V	9/17	1200	589
WL-19080255	GREEN	12V	9/17	1400	525
WL-19080257	BLUE	12V	9/17	700	470
WL-1908025W	WHITE	12V	9/17	1100	*
WL-19080350	RED	24V	9/17	1250	630
WL-19080352	YELLOW	24V	9/17	1200	589
WL-19080355	GREEN	24V	9/17	1400	525
WL-19080357	BLUE	24V	9/17	700	470
WL-1908035W	WHITE	24V	9/17	1100	*
WL-19080450	RED	28V	9/17	1250	630
WL-19080452	YELLOW	28V	9/17	1200	589
WL-19080455	GREEN	28V	9/17	1400	525
WL-19080457	BLUE	28V	9/17	700	470
WL-1908045W	WHITE	28V	9/17	1100	*
BLACK CHROME BEZEL					
WL-19081250	RED	12V	9/17	1250	630
WL-19081252	YELLOW	12V	9/17	1200	589
WL-19081255	GREEN	12V	9/17	1400	525
WL-19081257	BLUE	12V	9/17	700	470
WL-1908125W	WHITE	12V	9/17	1100	*
WL-19081350	RED	24V	9/17	1250	630
WL-19081352	YELLOW	24V	9/17	1200	589
WL-19081355	GREEN	24V	9/17	1400	525
WL-19081357	BLUE	24V	9/17	700	470
WL-1908135W	WHITE	24V	9/17	1100	*
WL-19081450	RED	28V	9/17	1250	630
WL-19081452	YELLOW	28V	9/17	1200	589
WL-19081455	GREEN	28V	9/17	1400	525
WL-19081457	BLUE	28V	9/17	700	470
WL-1908145W	WHITE	28V	9/17	1100	*

*Chromaticity coordinates X=0.31 Y=.032

**Luminous intensity data of the used LEDs at: I_{OP typ} DC

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm

OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

NOTES

- Maximum panel thickness 4mm
- Storage temperature T_{STG}: -25°C – +80°C
- Ambient temperature T_A: -20°C – +60°C
- AC/DC operation
- Voltage tolerance V_{OP}: ±10%
- Electro-optical ratings at T_A=25°C
- Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
- Mounting hole 8 + 0.2mm
- 2.8 x 0.8mm terminals are standard
- Due to production tolerances, slight color variations may be detected within individual consignments
- Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut
- CAUTION: Do not solder directly to terminals
- These Wamco indicators include a protection diode and can be used on DC and AC voltage. The typical light reduction on AC voltage is approx. 25%

CERTIFICATIONS

RoHS
COMPLIANT



P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-1908XX5X Series Rev 2