
PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.380"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
NEON 115VAC SERIES				
WL-6010QM1	RED	105-125VAC	1.5mA	25,000
WL-6010QM3	AMBER	105-125VAC	1.5mA	25,000
WL-6012QM5	GREEN	105-125VAC	1.5mA	25,000
NEON 230VAC SERIES				
WL-6011QM1	RED	208-250VAC	1.5mA	25,000
WL-6011QM3	AMBER	208-250VAC	1.5mA	25,000
WL-6013QM5	GREEN	208-250VAC	1.5mA	25,000

DIMENSIONAL CHARACTERISTICS



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

NOTES

- 1. Recommended panel thickness
 - 0.030" to 0.250"
- 2. .187" terminals are standard
- 3. Storage temperature

T_{STG}: -25°C - +100°C

- 4. Ambient temperature T_A : -20°C +100°C
- 5. Voltage tolerance V_{OP} : $\pm 10\%$
- Body material Nylon, white
- Lens material Polycarbonate
- 8. Bezel material Stainless steel
- 9. Terminals

Quick-connect, tinned brass

- 10. Gaskets Buna-N
- Mounting hardware (nut, lock washer, and gasket) included

CERTIFICATIONS

UL (E340667), RoHS





- Splash proof
- Outdoor applications
- NEMA 3-R



