

Honeywell Sensing and Control

V7-7B17D8-201



V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 11 A at 277 Vac, Roller Lever Actuator, 2,78 N [10.0 oz] Maximum Operating Force, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

V7 Series Features

- World-wide package size acceptance
- Current rating ranges from 0.1 A to 25 A
- Wiping contact action
- $\bullet\,$ Temperature range to 177 °C [350 ° F]
- · Long mechanical life
- Elongated mounting holes for easier, more accurate mounting
- UL/CSA recognized, ENEC (European) approval available
- Choice of actuation, termination and operating characteristics

Potential Applications

- Appliances
- Vending machines
- Timing devices
- Office equipment
- Computer/business
- equipment
- Test instruments
- Medical/dental equipment
- Communications equipment
- HVAC equipment
- Manually operated devices
- Valves
- Gaming equipment
- · Pressure switches

Description

MICRO SWITCH™ V5 and V7 Series basic switches are used for simple or precision on/off, end of limit, presence/absence, pressure, temperature and manual operator interface application needs.

Product Specifications	
Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	11 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Roller Lever
Termination	Quick Connect
Operating Temperature Range	-40 °C to 85 °C [-40 °F to 185 °F]
Voltage	277 Vac

Approvals	CSA,UL,ENEC
Actuator Length	20,6 mm [0.81 in]
Contact Type	Silver
Operating Force (O.F.)	2,78 N [10.0 oz] max.
Release Force (R.F.)	0,28 N [1.0 oz] min.
Pretravel (P.T.)	1,42 mm [0.056 in] max.
Overtravel (O.T.)	0,86 mm [0.034 in] min.
Differential Travel (D.T.)	0,33 mm [0.013] max.
Operating Position (O.P.)	20,5 ± 0,736 mm [0.808 ± 0.029 in]
Housing Material	PCT PolyesterThermoplastic
High Temperature	85 °C [185 °F]
CE mark	61058-1
UL File #	E12252
CSA File #	LR41370
Agency Approvals and Standards	1054
Mounting Centers	22,2 mm [0.88 in]
Maximum Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	16 mm [0.63 in]
Package Width	10,2 mm [0.40 in]
Package Length	27,7 mm [1.09 in]
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	V7

