

## Honeywell Sensing and Control



### AML24EBA2AC05



Actual product appearance may vary.

AML24 Series Rocker Switch, DPDT, 3 position, Silver Contacts, 0.110 in x 0.020 in (Solder or Quick-Connect), Non-Lighted, Rectangle, Snap-in Panel

#### Features

- Silver or gold contacts
- 2 or 3 position operation

• Lighted or nonlighted covers for switch housings

Toggle type rocker operators
permanently installed in rectangular
housings

- Lamps furnished installed or ordered separately
- Lamp circuit independent of switch
- circuit
- UL recognized
- CSA certified

#### Description

# Potential Applications

- Industrial machinery and
- equipmentCommercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Electronic control rectangular rocker switch housings. Available with one or two lamps or nonlighted displays. Housings have black paddles and bezels. Terminals are 0.110 in by 0.020 in, or 0.025 in by 0.025 in with silver or gold contacts. Switches have two or three position operating action, with one circuit on and one circuit off in extreme operating position. Rocker operators ordered separately.

	Product Specifications
Circuitry/ Operating action	Keyway Momentary Center Position Position Position $1 \ 2 \ 3 \ 1 \ 1 \ 2 \ 3 \ 1 \ 1 \ 1 \ 1 \ 1 \ 1 \ 1 \ 1 \ 1$
Product Type	MICRO SWITCH™ Rocker
Housing Type	Non-Lighted, Rectangle

Contact Type	Silver Contacts
Circuitry	DPDT
Action	3 position
Mounting	Snap-in Panel
Termination	0.110 in x 0.020 in (Solder or Quick-Connect)
Availability	Global
UNSPSC Code	302128
UNSPSC Commodity	302119 Switches and controls and relays
Series Name	AML24