

Honeywell Sensing and Control

ontrol

AML31FBA4AD

Image Not Available

AML31 Series, Solid State Pushbutton, Rectangular, Standard Bezel, Lighted, 1 Incandescent Lamp, DPST NO Form X, Alternate Action, Snap in panel mount

Features

- Snap-in Surface mount
- UL recognized, CSA certified
- Lamp circuit independent of switch circuit
- Metric design for world wide acceptance
- Buttons can be custom legend

Product Specifications	
Product Type	MICRO SWITCH™ Pushbutton
Housing Type	Rectangular
Circuitry	DPST NO Form X
Action	Alternate action
Mounting	Snap-in Panel
Lamp Type	Lighted, 1 Incandescent Lamp
Termination	.187 x .020 (Solder or Quick- Connect)
Ampere/Voltage Range (Resistive Load)	0.4-10 A @ 0.5-30 Vdc,0.4-10 A @ 0.5-250 Vac
LED/Lamp/Neon Voltage	No Lamp Installed
Comment	use AML51 button
Availability	Global
UNSPSC Code	30211913
UNSPSC Commodity	30211913 Push button switches
Series Name	AML31

