


MICRO SWITCH

MINNEAPOLIS-FLUORENCE REGULATOR COMPANY
 FREEPORT, ILLINOIS
 ED. MFR. CODE 91929


SWITCH - ENCLOSED

CATALOG LISTING
1CH32-R



CIRCUIT DIAGRAM

0
 573
 80
 7370
 SK
 AY 85
 53259
 SK
 PR 88
 8501
 M
 B 91



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF MINNEAPOLIS-FLUORENCE REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
RATING FORCE	6-12 LB
OVERTRAVEL FORCE	30 LB MAX
RELEASE FORCE	4 LB MIN
TRAVEL	.040 MAX
DIFFERENTIAL TRAVEL	.020 MAX
RETRAVEL	.250 MIN

ELECTRICAL DATA		
CONTACT ARRANGEMENT S P D T		
LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	

SCALE FULL	
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	
TOLERANCES ARE:	
ONE PLACE (.0)	± .030
TWO PLACE (.00)	± .018
THREE PLACE (.000)	± .008
ANGLES	±
WEIGHT	

NOTES

- 1 - SWITCH SEALED PER MIL-S-8805 SYMBOL 2
- 2 - CIRCUIT DIAGRAM, CATALOG LISTING AND DATE CODE ARE SHOWN ON NAMEPLATE
- 3 - CORROSION RESISTANT STEEL ENCLOSURE

△ HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805