

Honeywell Sensing and Control



1DM401



Snap-in Panel Mount Switch, Single Pole Double Throw (SPDT) Circuitry, 10 A at 277 Vac, Finger Grip Plunger Actuator, Silver Contacts, Quick Connect Termination

Actual product appearance may vary.

Features

- Attractive, rugged snap-in panel mount design easy installation
- Choice of momentary, alternate push-pull or pull-to-cheat operation
- Quick-connect terminals
- Expected mechanical life: 1 million operations, 95% survival
- UL recognized file #E22779, CSA certified file #LR4442

Description

The MICRO SWITCH[™] DM/DP Series are snap-action switches in basic and manual configurations. They have quick-connect terminals and snap-in, panel mount housings for ease of installation. They include momentary and alternate actions, and single- or double-pole. The DM accept a button for manual operation. The DP have plungers for basic operation.

Product Specifications	
Switch Type	Snap-in Panel Mount (0.55 in x 1.12 in panel cutout)
Sealed	No
Ampere Rating	10 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Finger Grip Plunger
Termination	Quick Connect
Operating Temperature Range	-37 °C to 82 °C [-35 °F to 180 °F]
Voltage	277 Vac
Approvals	CSA,UL
Contact Type	Silver

Potential Applications

- Appliance door lights
- Door interlocks
- Stop/start switches

Operating Force (O.F.)	4,17 N [15 oz] max.
Overtravel (O.T.)	13,2 mm [.520 in] min.
Free Position (F.P.)	17,8 mm [0.700 ± 0.030 in] max.
Housing Material	Polyester
CE mark	No
UL File #	E12252
CSA File #	LR4442
Agency Approvals and Standards	UL/CSA
Recommended For	Door Status Indication
Availability	Global
Series Name	DM/DP

