

# **Honeywell Sensing and Control**

## V7-2A17D8-207



Actual product appearance may vary.

V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 5 A at 250 Vac, Roller Lever Actuator, 0,42 N [1.5 oz] Maximum Operating Force, Silver Contacts, Quick Connect Termination

#### **V7 Series Features**

- World-wide package size acceptance
- Current rating ranges from 0.1 A to 25 A
- Wiping contact action
- $\bullet$  Temperature range to 177 °C [350 ° F]
- · Long mechanical life
- Elongated mounting holes for easier, more accurate mounting
- UL/CSA recognized, ENEC (European) approval available
- Choice of actuation, termination and operating characteristics

### **Potential Applications**

- Appliances
- Vending machines
- Timing devices
- Office equipment
- Computer/business equipment
- Test instruments
- Medical/dental equipment
- Communications equipment
- HVAC equipment
- Manually operated devices
- Valves
- Gaming equipment
- Pressure switches

## Description

MICRO SWITCH™ V5 and V7 Series basic switches are used for simple or precision on/off, end of limit, presence/absence, pressure, temperature and manual operator interface application needs.

Product Specifications	
Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	5 A
Circuitry	Single Pole Double Throw (SPDT)
Actuator	Roller Lever
Termination	Quick Connect
Operating Temperature Range	-40 °C to 82 °C [-40 °F to 180 °F]
Voltage	250 Vac
Approvals	CSA,UL,ENEC
Actuator Length	34,0 mm [1.34 in]
Contact Type	Silver

Operating Force (O.F.)	0,42 N [1.5 oz] max.
Release Force (R.F.)	0,03 N [0.10 oz] min.
Pretravel (P.T.)	2.92 mm [0.115 in] min.
Overtravel (O.T.)	1,52 mm [0.060 in] min.
Differential Travel (D.T.)	0,64 mm [0.025] max.
Operating Position (O.P.)	$20.6 \pm 1.27 \text{ mm } [0.810 \pm 0.050 \text{ in}]$
Housing Material	PCT PolyesterThermoplastic
High Temperature	85 °C [185 °F]
UL File #	E12252
CSA File #	LR41370
Agency Approvals and Standards	1054
Mounting Centers	22,2 mm [0.88 in]
Maximum Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	16 mm [0.63 in]
Package Width	10,2 mm [0.40 in]
Package Length	27,7 mm [1.09 in]
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	V7

