



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

## 50 Ohm RG-58 Molded BNC Cables

- Constructed with molded strain relief boot



Item #	Figure	Description
NBC-1503	FIG. 1	3 FT. 50 OHM RG-58 BNC (M-M) MOLDED CABLE
NBC-1506	FIG. 1	6 FT. 50 OHM RG-58 BNC (M-M) MOLDED CABLE
NBC-1512	FIG. 1	12 FT. 50 OHM RG-58 BNC (M-M) MOLDED CABLE

## 50 Ohm RG-58 Assembled BNC Cables

- Constructed with heat shrink tubing on ends
- Available in custom lengths and configurations



Item #	Figure	Description
RFC-1111	FIG. 2	1 FT. 50 OHM RG-58 BNC (M-M) CABLE
RFC-1113	FIG. 2	3 FT. 50 OHM RG-58 BNC (M-M) CABLE
RFC-1115	FIG. 2	7 FT. 50 OHM RG-58 BNC (M-M) CABLE
RFC-1116	FIG. 2	10 FT. 50 OHM RG-58 BNC (M-M) CABLE
RFC-1213	FIG. 3	3 FT. 50 OHM RG-58 BNC TO BNC RIGHT-ANGLE (M-M)
RFC-1215	FIG. 3	7 FT. 50 OHM RG-58 BNC TO BNC RIGHT-ANGLE (M-M)
RFC-1216	FIG. 3	10 FT. 50 OHM RG-58 BNC TO BNC RIGHT-ANGLE (M-M)
RFC-1313	FIG. 4	3 FT. 50 OHM RG-58 BNC (M-F) EXTN. CABLE
RFC-1315	FIG. 4	7 FT. 50 OHM RG-58 BNC (M-F) EXTN. CABLE
RFC-1316	FIG. 4	10 FT. 50 OHM RG-58 BNC (M-F) EXTN. CABLE

## 50 Ohm Assembled N Cables

- Available in RG-58, RG-11 & RG-213
- Constructed with heat shrink tubing on ends
- Available in custom lengths and configurations



Item #	Figure	Description
RFC-1813	FIG. 5	3 FT. 50 OHM RG-58 N (M-M) ASSEMBLED CABLE
RFC-1815	FIG. 5	7 FT. 50 OHM RG-58 N (M-M) ASSEMBLED CABLE
RFC-1816	FIG. 5	10 FT. 50 OHM RG-58 N (M-M) ASSEMBLED CABLE
RFC-1843	FIG. 6	3 FT. 50 OHM RG-11/213 N (M-M) ASSEMBLED CABLE
RFC-1845	FIG. 6	7 FT. 50 OHM RG-11/213 N (M-M) ASSEMBLED CABLE
RFC-1846	FIG. 6	10 FT. 50 OHM RG-11/213 N (M-M) ASSEMBLED CABLE