



PIN NO	A	B	C	D
09	16.25	25.00	30.80	19.20
15	24.65	33.30	39.20	27.70
25	38.40	47.00	53.00	41.20
37	54.80	63.50	69.40	57.30

NOTE
 MATERIAL
 INSULATOR: PBT +30%G.F.(UL94V-0)
 CONTACTS: BRASS OR PHOSPHOR BRONZE
 SHELL: SPCD
 CONTACT PLATING: GOLD PLATING OVER NICKEL
 ELECTRICAL SPECIFICATION
 CURRENT RATING: 5A;
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION RESISTANCE:1000MΩ MIN 500V DC.
 ENVIRONMENTAL
 OPERATING TEMPERATURE: -55°C~105°C.

				DESCRIPTION	D-SUB FEMALE SOLDER TYPE	SCALE	4 / 1	UNITS-MM	SRD	ANGLE
				MODEL NO						
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO	DSC-12XX					
		CJJ	CJJ	FINISHING			2011/07/12		A1	
				MATERIAL			DATE		REVISION	