



NOTE
 MATERIAL
 INSULATOR: PBT+30% GLASS FIBER (UL 94V-0) BLACK.
 CONTACTS: BRASS
 SHELL: SPCD
 CONTACT PLATING: GOLD PLATING OVER NICKEL
 ELECTRICAL SPECIFICATION
 CURRENT RATING: 5A;
 CONTACT RESISTANCE: 25m MAX.
 INSULATION RESISTANCE:1000M MIN 500V DC.
 ENVIRONMENTAL
 OPERATING TEMPERATURE: -55°C~105°C.

Shell Size	A±0.20	B±0.25	C±0.38	D±0.20
9	16.33	24.99	30.80	19.14
15	24.66	33.32	39.10	27.47
25	38.38	47.04	53.00	41.19
37	54.84	63.50	69.32	57.65
50	52.20	61.00	67.00	55.01

		DESCRIPTION	D-SUB FEMALE CRIMP TYPE	SCALE	4 / 1	UNITS:MM	SRD	ANGLE
		MODEL NO						
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO	DSC-22XX			
		CJJ	CJJ	FINISHING		△	2011/07/12	A1
				MATERIAL		SYM	DATE	REVISION