



SPECIFICATIONS:

				LENGTH TOLERANCE:	
Type	MM\10G	APC	SM	LENGTH (L)	TOLERANCE
Insertion Loss	≤ 0.5dB	≤ 0.3dB	≤ 0.2dB	< 1M	+50mm/-0
Return Loss	≥ 20dB	≥ 65dB	≥ 55dB	≥ 1M < 10M	+100mm/-0
Test Wavelength	850nm	1310nm	1310nm	≥ 10M < 30M	+150mm/-0
				≥ 30M	+1%/-0

 Tolerances unless otherwise specified:	Designed By		DESC.	SC-SC GENERIC
	Checked By			
	Approved By		DRG. No.	
Scale		 Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178 Tel: 305-513-8583 Fax: 305-513-9675 www.QuestTechnologyIntl.com		
Version	1.0			