

Raceway On-A-Roll®

Raceway On-A-Roll® is ideal for wiring security systems, telecom & datacom, and home theater installations. When pulled out of the box, Raceway On-A-Roll® is in its flat design, can be cut to exact size, and snaps together into a standard duct shape. The 1/2" and 1" Raceway On-A-Roll system is compatible with the accessory components of the WireHider System. It comes complete with a solvent based curing adhesive tape on the back for secure adhesion to the wall. It is an easy and efficient way to organize and conceal wires or cables of any kind. Packaged in a pizza box style dispenser its cut-to-length efficiency, provides 100% usable raceway.



R.O.A.R. Pull-Out Box

- Cut-to-Length Efficiency, fast & easy installation
- Compact Storage – 50 ft. or 100 ft. per Pull-Out Box
- Constructed of UL94V-0 flame retardant PVC
- Built with UV Stabilizer to prevent color fading
- Latex paintable PVC surface
- Solvent based adhesive tape for secure installation
- No waste, Use 100% of material



Size	Length	Qty	WHITE	BEIGE	Interior Width	Interior Height
1/4"	50 FT.	1 ROLL	FWF-25511	FWF-25521	0.255"	0.125"
	100 FT.	1 ROLL	FWF-25111	FWF-25121	0.255"	0.125"
3/8"	50 FT.	1 ROLL	FWF-14511	FWF-14521	0.375"	0.375"
	100 FT.	1 ROLL	FWF-14111	FWF-14121	0.375"	0.375"
3/8" Low Profile	50 FT.	1 ROLL	FWF-38511	FWF-38521	0.255"	0.125"
1/2"	50 FT.	1 ROLL	FWF-05511	FWF-05521	0.475"	0.475"
1"	50 FT.	1 ROLL	FWF-10511	FWF-10521	1.085"	0.545"

*Accessories available for 1/2" and 1" sizes of Raceway On-A-Roll®

WireHider® Cable Capacity Chart

WireHider®			1/2" Series			1" Series			1 1/2" Series		
Cable / Wire Size	Category/Designation	Cable OD	20%	40%	100%	20%	40%	100%	20%	40%	100%
Coaxial Cable	RG58	3.0mm	1	2	5	2	4	9	5	11	25
	RG59	6.0mm	0	1	2	1	2	5	3	7	15
	RG62	6.0mm	0	1	2	1	2	5	3	7	15
	RG6	7.0mm	0	1	2	1	2	5	2	5	11
	RG6 QUAD	7.5mm	0	1	2	1	2	5	2	5	11
Telephone & LAN	2-Pair, 24 AWG	4.0mm	2	4	9	4	8	18	10	21	45
UnShielded Twisted Pair (UTP)	3-Pair, 24 AWG	5.0mm	1	3	7	3	7	15	9	18	40
	4-Pair, 24 AWG	6.2mm	1	2	5	2	4	9	5	11	25
	25-Pair, 24 AWG	10.0mm	0	0	0	0	1	2	1	2	5
Telephone & LAN	2-Pair, 24 AWG	4.0mm	2	4	9	4	8	18	10	21	45
Shielded Twisted Pair (STP)	3-Pair, 24 AWG	5.0mm	1	3	7	3	7	15	9	18	40
	4-Pair, 24 AWG	6.2mm	1	2	5	2	4	9	5	11	25
	25-Pair, 24 AWG	10.0mm	0	0	0	0	1	2	1	2	5
HDMI	19Cond., 28AWG	7.5mm	0	1	2	1	2	5	2	5	11
USB	4 Cond., 28AWG	5.0mm	1	3	7	3	7	15	9	18	40
RCA (RGB)	3 Cond., 28AWG	10.0mm	1	2	5	2	4	9	5	11	25
Fiber Optic	Two Strand (Duplex), Multimode, 62.5/125um	3.0mm	1	2	5	2	4	9	5	11	25

STRUCTURED CABLING

FIBER OPTIC

WIRE & CABLE

RF COAXIAL

HDMI & AUDIO/VIDEO

WIRE MANAGEMENT

INSTALLATION TOOLS