


**Notes:**

1. Material: Nylon 6.6
2. Flammability Raing: UL94V-2
3. Maximum Operating Temp. 185F (85C)
4. Minimum Tesnile Rating: 18 lbs.
5. Maximum Bundle Diameter (Noted Below)
6. UL 62275 Type 2/21
7. Min. Installation Temp. -0C (32F)

<b>Material Designations:</b> -9 = Natural -# = Color -0 = UV Black -HS= Heat Stabilized Black	 Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178 Tel: 305-513-8883 Fax: 305-513-9876 www.QuestTechnologyIntl.com		<b>Miniature Cable Tie 18 LB. Series</b>	
			<b>Maximum Bundle Dia.</b>	<b>A</b>
			31.75 (1.25)	6.125
		50.8 (2.0)		8.125
Unless Otherwise Specified All dimensions are in inches.	<b>SIZE</b> <b>A</b>	<b>FSCM NO.</b>	<b>DWG NO.</b> <b>NWT-808X</b>	<b>REV</b> <b>2</b>
	<b>SCALE</b> N/A		Material Nylon 6/6	<b>SHEET</b> 1 of 1