



PARAMETERS

NO	Product introduction
1	Zinc alloy die casting products.
2	Surface plating colorful
3	Glue sealing cover
4	Inch thread F head
5	To fix the main body on both sides
6	achieve good sealing performance and anti jamming ability
7	Internal use direct connectivity

PARAMETERS

ITEM NO	SPEC	FREQUENCY RANGE	INSERTION LOSS (dB)	ISOLATION (dB)	RETURN LOSS (dB)
VSP-1220	5-900MHZ	5-47MHZ	-4.2dB	-13dB	-10dB
		47-470MHZ	-4.6dB	-13dB	-10dB
		470-860MHZ	-5.2dB	-12dB	-10dB
		860-900MHZ	-5.8dB	-12dB	-10dB



Quest Technology Int'l, Inc.
 11200 NW 138th St., Medley, FL 33178
 Tel: 305-513-8583 Fax: 305-513-9675
 www.QuestTechnologyintl.com

ITEM	VSP-1220	Date	2016.07.05
SCALE	1:1	UNITS	mm
length tolerance: ±0.5mm tolerance			