


# PARAMETERS

ITEM NO.	SPEC.	FREQUENCY RANGE	INSERTION LOSS (DB)	ISOLATION (DB)	RETURN LOSS (DB)
		5-47MHZ	7.0 ± 1DB	14 ± 1DB	12 ± 1DB
VSP-1420	5-900MHZ	47-470MHZ	7.5 ± 1DB	15 ± 1DB	12 ± 1DB
1 PORTS					
POWER PASS		470-860MHZ	8.2 ± 1DB	15 ± 1DB	10 ± 1DB
		860-900MHZ	8.4 ± 1DB	18 ± 1DB	10 ± 1DB

NO.	Q' TY	DESC.	MATERIAL
1	1	Housing	Zinc-Alloy, Chromate plated
2	1	Back plate	Iron, Nickel/Nickel
3	5	F-Port	Zinc-Alloy, Chromate plated
4	2	Mounting screws	Iron, Chromate plated

 Quest Technology Int'l, Inc. 11200 NW 138th St., Medley, FL 33178 Tel: 808-518-8680 Fax: 808-518-9876 www.QuestTechnology.com		DESCRIPTION		4 WAY SPLITTER	
		PART NO		VSP-1420	
DRAW		JACKY		CONSUMER	
CHECK		DATE		2016/07/04	REV.
APP.		SHEET		1/1	UNIT mm SCALE 1:1