




## SKINTOP® Strain Relief Cord Connectors SKINTOP® SLN & SLRN FLEX






SKINTOP® FLEX is a liquid tight, spiral strain relief that offers additional safety against overstress and conductor breakage. Ideally suited for hand held equipment, moving machinery and robotics.

## **Application Advantage:**

- Superior bending protection for cable conservation and functional reliability
- The heavy duty SKINTOP® design provides great pullout strength and very reliable strain relief
- Superior integrated locking mechanism includes an internal ratchet for vibration proof protection
- Multi-trapezoidal thread requires just one twist to tighten
- Generous high quality neoprene bushing provides a liquid tight and dust proof, hermetic seal





## TECHNICAL DATA:

Materials:

Body: Polyamide

Bushing: CR

Color: Black (RAL 9005) UV Resistant

Gray (RAL 7001)

Lt. Gray (RAL 7035) available upon request

Protection Seal: 70 PSI

IP 68, 5 Bar

**Exceeds NEMA 6/6P Pressure rating** 

Temperature Range: -20°C to +80°C

Part Number	Thread Type	UL Status	Clamping Range ØF inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. Ibs.
NPT Thread- Black								
S2338	NPT-3/8"	R	.138315	0.748	3.228	0.591	100	3.00
S2312	NPT-1/2"	L	.197472	0.945	4.094	0.591	100	5.50
S2334	NPT-3/4"	L	.512709	1.299	5.236	0.591	50	12.00
NPT Thread	d- Gray							
S1338	NPT-3/8"	R	.138315	0.748	3.228	0.591	100	3.00
S1312	NPT-1/2"	L	.197472	0.945	4.094	0.591	100	5.50
S1334	NPT-3/4"	L	.512709	1.299	5.236	0.591	50	12.00
NPT Thread with Reducer Bushing-Black								
S2438	NPT-3/8"	R	.079236	0.748	3.228	0.591	100	3.00
S2412	NPT-1/2"	L	.157354	0.945	4.094	0.591	50	5.50
S2434	NPT-3/4"	L	.354630	1.299	5.236	0.591	25	12.00
NPT Thread with Reducer Bushing-Gray								
S1438	NPT-3/8"	R	.079236	0.748	3.228	0.591	100	3.00
S1412	NPT-1/2"	L	.157354	0.945	4.094	0.591	50	5.50
S1434	NPT-3/4"	L	.354630	1.299	5.236	0.591	50	12.00

UL Status: R = Recognized; L = Listed