

EPIC® Rectangular Connectors

Complete your Installation with a SKINTOP®

Your installation can be completed with an SKINTOP®. EPIC® Connectors mate with SKINTOPS® without locknuts. Use of tapered (NPT) threads is not recommended with EPIC® Rectangular Connectors

SKINTOP® SL: PG Liquid Tight Non-Metallic Strain Relief Connector



Part Number		Thread Type & Size
without Locknut	with Locknut	
53015130	S1113	PG-13
53015140	S1116	PG-16
53015150	S1121	PG-21
53015160	S1129	PG-29
53015170	S1136	PG-36
53015180	S1142	PG-42

SKINTOP® MS: PG Liquid Tight Metallic Strain Relief Connector



Part Number	Thread Type & Size
52015730	PG-13
52015740	PG-16
52015750	PG-21
52015760	PG-29
52015765	PG-36
52015766	PG-42

SKINTOP® SLM: Metric Liquid Tight Non-Metallic Strain Relief Connector



Part Number		Thread Type & Size
without Locknut	with Locknut	
53111020	S1513	M-20X1.5
53111030	S1516	M-25X1.5
53111040	S1521	M-32X1.5
53111050	S1529	M-40X1.5
53111060	S1536	M-50X1.5

SKINTOP® MS-M: Metric Metallic Strain Relief Connector



Part Number	Thread Type & Size
53112020	M-20X1.5
53112030	M-25X1.5
53112040	M-32X1.5
53112050	M-40X1.5
53112060	M-50X1.5