# **EPIC® Rectangular Connectors**



MC Series Plugs & Receptacles

## ETHERNET MODULE- RJ 45 Connectors + 4 Power Contacts



Power Contacts:
Rated Voltage:
600V

Rated Current: 10A

Occupies two module positions in frame. Uses standard HD Series Machined Crimp Contacts for Power. RJ 45 plug not included.

RJ 45 connector part number- CE6326

Plug	Receptacle	
10344300	10345300	

### **EPIC® Universal Bus Modules**



#### Technical Data:

- Screw Terminated
- Transfer rate max. 1.5 MB/s for bus feed through
- Rated Voltage: 30VRated Current: 1A

Plug: 4+Shield	Receptacle: 4+Shield	
10390600	10390700	

# **EPIC® Pneumatic Modules**

These modules are used for easy and fast connection of compressed air hoses. Applications include machine building, mini pneumatics, measurement and control technology.

#### Technical Data:

- Available with 1 or 2 Connector Pins
- For compressed air hoses with inner diameter of 2.5 mm or 4 mm. Outer diameter max. 8.0 mm
- Female Version has built in blocking valve
- Air pressure: Max. 10 bar (145 psi)
- Temperature Range: -20°C to 100°C









Part Number	Description	Contacts	Hose Diameter
44424004	Male	1	2.5 mm
44424005	Female with built in valve	1	2.5 mm
44424006	Male	1	4.0 mm
44424007	Female with built in valve	1	4.0 mm
44424008	Male	2	2.5 mm
44424009	Female with built in valve	2	2.5 mm
44424010	Male	2	4.0 mm
44424011	Female with built in valve	2	4.0 mm

