

AP9872

Power Cords

Pwr Cord, 15A, 100-120V, C19 to 5-15



[+ More Images](#)

APC Power Cords , Input: 120V , Input Connections: NEMA 5-15P , Cord Length: 8.2 feet (2.5 meters) , Output Connections: IEC 320 C19

Standard Lead Time: Usually in Stock

Technical Specifications

Product Overview

Output

Output Connections

(1) IEC 320 C19

Overload Protection

No

Input

Nominal Input Voltage

120V

Input Frequency

50/60 Hz

Input Connections

NEMA 5-15P



Cord Length

2.5 meters

Number of Power Cords

1

Acceptable Input Voltage

100-120 VAC

Maximum Line Current per phase

15A

Maximum Input Current per phase

15A

Load Capacity

1800 VA

Physical

Net Weight

0.23 KG

Maximum Height

89.00 mm

Maximum Width

216.00 mm

Maximum depth

89.00 mm

Shipping Weight

0.30 KG

Shipping Height

102.00 mm

Shipping Width

318.00 mm

Shipping Depth

108.00 mm

Color

Black

Environmental

Operating Environment

0 - 45 °C

Operating Relative Humidity

0 - 95%

Operating Elevation

0-3000 meters

Storage Temperature

-25 - 65 °C

Storage Relative Humidity

0 - 95%

Storage Elevation

0-15000 meters

Conformance

Regulatory Approvals

CSA,UL Listed

Standard Warranty

2 years repair or replace