

Select Your Country/Region

Search

HomeProductsSupportServicesSelectorsHow to Buy

APC Smart-UPS XL 750VA USB & Serial 120V

APC Smart-UPS XL, 750VA/600W, Input 120V/Output 120V, Interface Port DB-9 RS-232, SmartSlot, USB, Extended runtime model

Includes: CD with software, Smart UPS signalling RS-232 cable, USB cable, User Manual

Part Number : SUA750XL

Configure Now

Compare Models

Runtime Chart

Email Technical Specifications



Additional Information

Input Connection Type

Input voltage range for main operations

Cord Length

Product Overview
User Manual & Installation Guides
Product Distribution





[+] More Images

Technical Specifications

□ Output	
Output power capacity	750 VA
Output power capacity	600 Watts
Max Configurable Power	750 VA
Max Configurable Power	600 Watts
Nominal output voltage	120V
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal,57 - 63 Hz for 60 Hz nominal
Crest Factor	up to 5:1
Waveform type	Sine wave
·· ··· · · · · · · · · · · · · · · · ·	Sille wave
Output Connections	(8) NEMA 5-15R
, .	

NEMA 5-15P

82 - 144V

6 feet (1.83 meters)

Options:

- O Automatic Transfer Switches
- o <u>Batteries</u>
- Interface Connections
- O Management Devices
- O Rack Power Distribution
- O Replacement Battery Cartridges
- Services
- O <u>Software</u>

Features:

USB connectivity

General Features:

- Adjustable voltage sensitivity
- O Adjustable voltage-transfer points
- Audible alarms
- Automatic restart of loads after UPS shutdown
- Automatic self-test
- O Boost and Trim Automatic Voltage Regulation (AVR)
- Cold-start capable
- O Disconnected battery notification
- O Generator compatible
- O Hot-swappable batteries
- O Intelligent battery management
- LED status indicators
- O Network manageable
- O Plug-and-Play external batteries
- Power conditioning
- O Predictive failure notification

Input voltage adjustable range for mains operation	75 - 154V
□ Batteries & Runtime	
Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte: leakproof
Replacement battery cartridge	RBC7
RBC™ Quantity	1
Typical backup time at half load	50.6 minutes (300 Watts)
Typical backup time at full load	16.6 minutes (600 Watts)
Runtime Chart	Smart-UPS XL
Extended run options	APC Smart-UPS XL 750VA USB & Serial 120V
☐ Communications & Management	
Interface port	DB-9 RS-232,SmartSlot,USB
Available Smart Slot Interface Quantity	1
Control panel	LED status display with load and battery bar- graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Audible alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional
Surge Protection and Filtering Surge energy rating	459 Joules
Filtering	Full time multi-pole noise filtering: 0.3% IEEE surge let-through: zero clamping response time: meets UL 1449
□ Physical	
Maximum height	8.50 inches (216 mm)
Maximum width	6.70 inches (170 mm)
Maximum depth	17.30 inches (439 mm)
Net weight	53.00 lbs. (24.09 kg)
Shipping Weight	58.00 lbs. (26.36 kg)
Shipping Height	15.25 inches (387 mm)
Shipping Width	12.60 inches (320 mm)
Shipping Depth	23.25 inches (591 mm)
Color	Black
Units per Pallet	24.00
□ Environmental	
Operating Environment	0 - 40 °C (32 - 104 °F)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

- Resettable circuit breakers
- Safety-agency approved
- Scalable runtime
- Serial Connectivity SmartSlot
- Temperature-compensated battery charging more details....

opology: Line Interactive

Online thermal dissipation	100 BTU/hr
□ Conformance	
Approvals	BSMI,CSA,FCC Part 15 Class A,UL 1778
Standard warranty	2 years repair or replace

Copyright © American Power Conversion Corp., all rights reserved About APCInvestorsJob SeekersPressFeedbackContactPrivacy Policy