

APC Workshop SurgeArrest 8 Outlets

Part Number: PDIY8




Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15A
Cord Length	4.57 meters



Surge Protection and Filtering

Surge energy rating	800 Joules
eP Joule Rating	820
Let Through Voltage Rating	< 330

Physical

Net Weight	1.10 KG
------------	---------

Maximum Height	343.00 mm
Maximum Width	121.00 mm
Maximum Depth	44.00 mm
Shipping Weight	1.12 KG
Shipping Height	343.00 mm
Shipping Width	121.00 mm
Shipping Depth	74.00 mm
Master Carton Units	12.00
Master Carton Dimensions (Length x Width x Height)	18771 x 9881 x 5334 mm
Master Carton Weight	14.90 KG
SCC Codes	1073130423833 8
Color	Yellow
Units per Pallet	180.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters

Conformance

Regulatory Approvals	CSA,UL 1449
Standard Warranty	3 years repair or replace,Lifetime
UL 1449 TVSS Rating	330V