



APC Essential SurgeArrest, 6 outlets, 4 ft cord, metal housing, 120V

Part Number: P6M




Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	1.22 meters
Maximum Input Current	15A
Input Breaker Capacity	15A



Surge Protection and Filtering

Surge energy rating	540 Joules
Let Through Voltage Rating	< 330

Physical

Net Weight	0.70 KG
Maximum Height	311.00 mm

Maximum Width	63.00 mm
Maximum Depth	38.00 mm
Shipping Weight	0.80 KG
Shipping Height	335.00 mm
Shipping Width	100.00 mm
Shipping Depth	1168.00 mm
Master Carton Units	12.00
Master Carton Dimensions (Length x Width x Height)	394 x 229 x 324 mm
Master Carton Weight	11.00 KG
SCC Codes	1073130424827 6
Color	Grey
Units per Pallet	288.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters

Conformance

Standard Warranty	Lifetime
UL 1449 TVSS Rating	330V