



# APC Essential SurgeArrest 6 Outlets with Phone Protection 10FT Cord 120V Metal


Part Number: P6TM10



## Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

## Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P 
Cord Length	3.05 meters
Maximum Input Current	15A
Input Breaker Capacity	15A

## Surge Protection and Filtering

Surge energy rating	540 Joules
Data Line Protection	RJ-11 Modem/Fax protection
Let Through Voltage Rating	< 330

## Physical

Net Weight	0.70 KG
------------	---------

Maximum Height	311.00 mm
Maximum Width	63.00 mm
Maximum Depth	38.00 mm
Shipping Weight	0.80 KG
Shipping Height	335.00 mm
Shipping Width	100.00 mm
Shipping Depth	1168.00 mm
Master Carton Units	12.00
Master Carton Dimensions (Length x Width x Height)	394 x 229 x 324 mm
Master Carton Weight	11.00 KG
SCC Codes	1073130425321 8
Color	Grey
Units per Pallet	288.00

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters

## Conformance

Standard Warranty	Lifetime
UL 1449 TVSS Rating	330V