

## Basic Rack PDU

### Rack PDU, Basic, 1U, 30A, 208V, (10) C13



APC Basic Rack PDU , Input: 200V, 208V, 230V , Input Connections: NEMA L6-30P , Cord Length: 12 feet ( 3.66 meters ) , Output: 208V




**Includes:** Installation guide, Rack Mounting brackets, User Manual

**Standard Lead Time:** Usually in Stock

#### Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	24A
Always on Outlets	10
Overload Protection	Yes

#### Input

Nominal Input Voltage	200V,208V,230V	
Input Frequency	50/60 Hz	
Regulatory Derated Input Current (North America)	24A	
Input Connections	NEMA L6-30P	
Cord Length	3.66 meters	
Number of Power Cords	1	
Acceptable Input Voltage	200-240 VAC	
Maximum Line Current per phase	30A	
Maximum Input Current per phase	30A	
Load Capacity	4992 VA	

#### Physical

Net Weight	2.55 KG
Maximum Height	43.00 mm
Maximum Width	444.00 mm
Maximum Depth	77.00 mm
Shipping Weight	3.64 KG
Shipping Height	171.00 mm
Shipping Width	483.00 mm
Shipping Depth	174.00 mm
Color	Black
Units per Pallet	1.00

#### Environmental

Operating Environment	-15 - 45 °C
Operating Relative Humidity	5 - 95%
Operating Elevation	0-4500 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95%
Storage Elevation	0-15000 meters

#### Conformance

Regulatory Approvals	cUL Listed,CSA,UL 60950,UL Listed
Standard Warranty	2 years repair or replace
Environmental Compliance	RoHS