



APC Replacement Battery Cartridge #48
Part Number: RBC48



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity
168

Battery Type
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting
Stand alone battery stack

Battery manufacturer
--

Expected Battery Life (years)
3 - 5

RBC™ Quantity
1

Battery blocks per string
2

Physical

Net Weight
11.00 lbs. (5.00 kg)

Maximum Height
4.25 inches (108 mm)

Maximum Width
5.20 inches (132 mm)

Maximum Depth
5.90 inches (150 mm)

Shipping Weight
13.00 lbs. (5.91 kg)

Shipping Width
6.60 inches (168 mm)

Shipping Height
6.60 inches (168 mm)

Shipping Depth
8.80 inches (224 mm)

Units per Pallet
40.00

Environmental

Operating Environment
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity
0 - 95%

Operating Elevation 0-10000 feet (0-3000 meters)
Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
Conformance
Standard Warranty 1 year repair or replace
Sustainable Offer Status
RoHS Compliant
REACH REACH: Contains No SVHCs
PEP Available in Documentation tab
EOLI Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.