

SurgeArrest Essential

APC Power-Saving Essential SurgeArrest, 7 Outlets, 120V



Basic Protection for Computers and Electronics


Includes: User Manual

Standard Lead Time: Usually in Stock

Output

Number of Outlets	7
Receptacle Style	NEMA 5-15R

Input

Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P 
Cord Length	1.22 meters
Maximum Input Current	15A

Surge Protection and Filtering

Surge energy rating	1020 Joules
Peak Current Common Mode	72 kAmps
NM Surge Response Time (ns)	1 ns
Let Through Voltage Rating	< 400

Physical

Net Weight	0.45 KG
Maximum Height	387.00 mm
Maximum Width	71.00 mm
Maximum Depth	36.00 mm
Shipping Weight	0.80 KG
Shipping Height	489.00 mm

Shipping Width	178.00 mm
Shipping Depth	41.00 mm
Master Carton Units	6.00
Master Carton Dimensions (Length x Width x Height)	352 x 263 x 541 mm
Master Carton Weight	6.15 KG
SCC Codes	1073130426924 0
Color	White
Units per Pallet	198.00

Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters

Conformance

Regulatory Approvals	ETL,UL 1449
Standard Warranty	Lifetime
UL 1449 TVSS Rating	<400V
Environmental Compliance	RoHS