

ProtectNet

APC Surge Module for Digital Phone Line (T1, CSU, DSU, ISDN, DLL), Replaceable, 1U, for PRM4, PRM24



Advanced Protection Against Damaging Power Transients Traveling Over Computer, AV and Network Data Lines



Includes: User Manual

Standard Lead Time: Usually in Stock

Output

Number of Outlets	1
-------------------	---

Surge Protection and Filtering

Peak Current Normal Mode	0.20 kAmps
Peak Current Common Mode	0.25 kAmps
NM Surge Response Time (ns)	1 ns
Data Line Protection	RJ45 ISDN / T1 protection
Data Lines Protected (multi-line only)	1-8
Let Through Voltage Rating	< 60

Physical

Net Weight	0.02 KG
Maximum Height	44.00 mm
Maximum Width	19.00 mm
Maximum Depth	69.00 mm
Shipping Weight	0.05 KG
Shipping Height	99.00 mm
Shipping Width	33.00 mm
Shipping Depth	95.00 mm
Master Carton Units	96.00
Master Carton Dimensions (Length x Width x Height)	25.125 X 16.25 X 8.125 inches
Master Carton Weight	15.00 lbs.
SCC Codes	3073130420337 8
Color	Black

Environmental

Operating Environment	-15 - 45 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-3000 meters

Conformance

Regulatory Approvals	cUL Recognized,CE,UL 497A,VDE
Standard Warranty	Lifetime
Environmental Compliance	RoHS