



**APC Replacement Battery Cartridge #10**  
Part Number: RBC10



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

**Batteries & Runtime**

Battery Volt-Amp-Hour Capacity  
54

Battery Type  
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting  
Stand alone battery stack

Expected Battery Life (years)  
3 - 5

RBC™ Quantity  
1

**Physical**

Net Weight  
3.60 lbs. (1.64 kg)

Maximum Height  
1.90 inches (48 mm)

Maximum Width  
4.00 inches (102 mm)

Maximum Depth  
5.50 inches (140 mm)

Shipping Weight  
4.00 lbs. (1.82 kg)

Shipping Width  
6.70 inches (170 mm)

Shipping Height  
2.40 inches (61 mm)

Shipping Depth  
8.10 inches (206 mm)

Color  
Black

Units per Pallet  
150.00

**Environmental**

Operating Environment  
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity  
0 - 95%

Operating Elevation  
0-10000 feet (0-3000 meters)

Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
<b>Conformance</b>
Standard Warranty 1 year repair or replace
<b>Sustainable Offer Status</b>
RoHS Compliant
PEP Available in Documentation tab
EOLI Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.