



APC Replacement Battery Cartridge #17
Part Number: RBC17



[Technical Specifications](#) [Product Overview](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity
108

Battery Type
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting
Stand alone battery stack

Expected Battery Life (years)
3 - 5

Battery Placement
Internal Battery

RBC™ Quantity
1

Physical

Net Weight
5.70 lbs. (2.59 kg)

Maximum Height
2.56 inches (65 mm)

Maximum Width
3.72 inches (94 mm)

Maximum Depth
5.95 inches (151 mm)

Shipping Weight
6.30 lbs. (2.86 kg)

Shipping Width
6.90 inches (175 mm)

Shipping Height
3.50 inches (89 mm)

Shipping Depth
8.40 inches (213 mm)

Color
Black

Units per Pallet
150.00

Environmental

Operating Environment
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity
0 - 95%

Operating Elevation 0-10000 feet (0-3000 meters)
Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
Conformance
Standard Warranty 1 year repair or replace
Sustainable Offer Status
RoHS Compliant
REACH REACH: Contains No SVHCs
PEP Available in Documentation tab
EOLI Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.