



APC Replacement Battery Cartridge #23
Part Number: RBC23



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity
336

Battery Type
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting
Enclosed battery cartridge

Expected Battery Life (years)
3 - 5

RBC™ Quantity
1

Physical

Net Weight
22.00 lbs. (10.00 kg)

Maximum Height
3.25 inches (83 mm)

Maximum Width
8.50 inches (216 mm)

Maximum Depth
13.50 inches (343 mm)

Shipping Weight
24.00 lbs. (10.91 kg)

Shipping Width
14.50 inches (368 mm)

Shipping Height
6.00 inches (152 mm)

Shipping Depth
19.50 inches (495 mm)

Color
Black

Units per Pallet
18.00

Environmental

Operating Environment
32 - 113 °F (0 - 45 °C)

Operating Relative Humidity
0 - 95%

Operating Elevation
0-10000 feet (0-3000 meters)

Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
Conformance
Standard Warranty 1 year repair or replace
Sustainable Offer Status
RoHS Compliant
REACH REACH: Contains No SVHCs
PEP Available in Documentation tab
EOL Available in Documentation tab
Other Environmental Compliance China RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.