



**APC Replacement Battery Cartridge #32**  
Part Number: RBC32



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

**Batteries & Runtime**

Battery Volt-Amp-Hour Capacity  
164

Battery Type  
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting  
Enclosed battery cabinet

Expected Battery Life (years)  
3 - 5

Battery Placement  
Internal Battery

RBC™ Quantity  
1

Battery blocks per string  
2

**Physical**

Net Weight  
11.73 lbs. (5.33 kg)

Maximum Height  
7.75 inches (197 mm)

Maximum Width  
5.88 inches (149 mm)

Maximum Depth  
2.50 inches (64 mm)

Shipping Weight  
13.00 lbs. (5.91 kg)

Shipping Width  
9.00 inches (229 mm)

Shipping Height

12.00 inches (305 mm)
Shipping Depth
4.00 inches (102 mm)
Color
Charcoal
<b>Environmental</b>
Operating Environment
32 - 104 °F (0 - 40 °C)
Operating Relative Humidity
0 - 95%
Operating Elevation
0-50000 feet (0-15000 meters)
Storage Temperature
32 - 104 °F (0 - 40 °C)
Storage Relative Humidity
0 - 95%
Storage Elevation
0-10000 feet (0-3000 meters)
<b>Conformance</b>
Standard Warranty
1 year repair or replace
<b>Sustainable Offer Status</b>
RoHS
Compliant
REACH
REACH: Contains No SVHCs
PEP
Available in Documentation tab
EOLI
Available in Documentation tab
Other Environmental Compliance
China RoHS

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.