



APC Replacement Battery Cartridge #35
Part Number: RBC35



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Battery manufacturer	--
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

Physical

Net Weight	3.08 lbs. (1.40 kg)
Maximum Height	2.60 inches (66 mm)
Maximum Width	2.28 inches (58 mm)
Maximum Depth	5.28 inches (134 mm)
Shipping Weight	3.68 lbs. (1.68 kg)
Shipping Width	5.76 inches (146 mm)
Shipping Height	3.70 inches (94 mm)
Shipping Depth	7.38 inches (187 mm)
Color	Black

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)

Storage Relative Humidity
0 - 95%

Storage Elevation
0-50000 feet (0-15000 meters)

Conformance

Standard Warranty
1 year repair or replace

Sustainable Offer Status

PEP
Available in Documentation tab

EOLI
Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.