



**APC Replacement Battery 12V-7AH**  
Part Number: RBC40



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

**Output**

battoutvolt  
12.0

**Batteries & Runtime**

Battery Volt-Amp-Hour Capacity  
87

Battery Type  
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting  
Stand alone battery stack

Expected Battery Life (years)  
3 - 5

RBC™ Quantity  
1

**Physical**

Net Weight  
5.50 lbs. (2.50 kg)

Maximum Height  
1.90 inches (48 mm)

Maximum Width  
4.00 inches (102 mm)

Maximum Depth  
5.50 inches (140 mm)

Shipping Weight  
6.10 lbs. (2.77 kg)

Shipping Width  
6.90 inches (175 mm)

Shipping Height  
3.50 inches (89 mm)

Shipping Depth  
8.40 inches (213 mm)

Color  
Black

Units per Pallet  
150.00

**Sustainable Offer Status**

PEP  
Available in Documentation tab

EOLI

---

Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.