



APC Replacement Battery Cartridge #43
Part Number: RBC43



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity
480

Battery Type
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting
Enclosed battery cartridge

Expected Battery Life (years)
3 - 5

RBC™ Quantity
1

Physical

Net Weight
42.00 lbs. (19.09 kg)

Maximum Height
3.00 inches (76 mm)

Maximum Width
8.50 inches (216 mm)

Maximum Depth
21.00 inches (533 mm)

Shipping Weight
45.00 lbs. (20.45 kg)

Shipping Width
15.50 inches (394 mm)

Shipping Height
9.00 inches (229 mm)

Shipping Depth
30.25 inches (768 mm)

Units per Pallet
12.00

Environmental

Operating Environment
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity
0 - 95%

Operating Elevation
0-10000 feet (0-3000 meters)

Storage Temperature
5 - 113 °F (-15 - 45 °C)

Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
Conformance
Standard Warranty 1 year repair or replace, 30 days (Japan only)
Sustainable Offer Status
RoHS Compliant
REACH REACH: Contains No SVHCs
PEP Available in Documentation tab
EOLI Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.